




NEW

Rotary Shaker

For mixing and preparing soil samples



MADE IN GERMANY

Rotary Shaker RS 10

360° overhead movement for complete mixing of samples

NEW



- Robust rotary shaker for up to 10 bottles à max. 3 kg
- Suitable for bottles and vessels up to 145 mm in diameter (round or square)
- Possibility to fasten a wide variety of vessels with a maximum height of 300 mm via the variable clamping system (adjustable in 15 mm increments)
- Quick and easy bottle change via a simple fastening method with individual fixing screws
- Forward / backward rotation for optimal mixing
- Safety shut-off when the door is opened
- Programmable control with touch display
- 10 individually definable shaking programs with adjustable start delay
- Option: base cabinet for storing samples, bottles or accessories



Technical Data Rotary Shaker RS 10

	Rotary Shaker RS 10
Article Number	6143 000
Shaking motion	360° overhead movement (variable direction)
Shaking platform (w x d)	280 x 750 mm
Max. load	30 kg
Height of vessels	170 - 300 mm
Diameter of vessels	max. 145 mm (round or square)
Diameter of lid	max. 100 mm
Fixation	variable fixing screws
Shaking speed	4 - 22 rpm, in steps of 1
Runtime	programmable / continuous
Relative humidity	~ 85 %
Ambient temperature	5 °C – 50 °C
Electrical supply	230 V, 50/60Hz
Enclosure protection	IP 21
Dimensions (w x d x h)	1160 x 550 x 570 mm
Weight	65 kg
Scope of delivery	Basic device incl. fixing screws for 10 bottles up to a height of max. 300 mm

B Edmund
Bühler

Edmund Bühler GmbH

Schindäckerstraße 8
72411 Bodelshausen / Germany
Phone: +49 7471 9864-0
info@edmund-buehler.de

Version 03/2024
Subject to technical alterations and mistakes.

www.edmund-buehler.de

